

KNIPEX Quality – Made in Germany



# Automatic Stripping Pliers

For multicore cable Ø 4.4 to Ø 7.5 mm with irregular sheathing cross-section

For control and sensor cables / actuator cables

Scale for the consistent stripping of standard lengths



Special cutter design for the accurate stripping of tough cable sheathing

Slide cable through and strip lengths as required



### Automatic Stripping Pliers

For multicore cable Ø 4.4 to Ø 7.5 mm with irregular sheathing cross-section


12

- ▶ For control and sensor cables / actuator cables, also for stripping flexible 3-core feed cables and extension cable
- ▶ Automatic adjustment to cable diameters between 4.4 and 7.5 mm
- ▶ No damage to the inner conductor or shield braid

- > For oil-resistant, halogen-free control and sensor / actuator cables with multicore cable design, shielded and unshielded
- > Suitable for highly flexible TPE-U-pipes, PUR and PVC cable sheathing, rubber leads such as H05 etc.
- > Long stripping lengths possible
- > Body: plastic, fibreglass-reinforced
- > Exchangeable blade: special tool steel, oil-hardened



12 74 180



Sectional view of an extension lead



Required stripping length easy to read off



Complex cutter design for precise and damage-free stripping of round cables

Article No.	EAN 4003773-	↔ mm	Stripping capacities Ø mm	⚖ g
12 74 180 SB	082323	175	4.4 - 7.5	120
12 79 31	082682	1 pair of spare blades for 12 74 180 SB		