



- Superior adhesive for long term reliability
- 2-up mount configuration speeds liner removal and installation
- 4-way cable tie entry makes part orientation fast and easy
- Adhesive backing allows routing of wires and cables where mounting holes cannot be drilled
- Used with *PANDUIT*® cable ties for a complete wire routing solution

‡ Cable Tie Cross Section Sizes: M = Miniature, I = Intermediate, S = Standard, HS = Heavy-Standard, LH = Light-Heavy, H = Heavy, HLM = Miniature *Tak-Ty*® Hook & Loop Cable Ties.

Part Number: ABM3H-A-L
Product Family: 4-Way Adhesive Backed Cable Tie Mounts
Product Line: Adhesive Backed

Product Line: Adhesive Mounts

RoHS Compliancy Status: Compliant

Part Description: 4-Way Adhesive Backed Cable Tie Mount

Product Type: Cable Tie Mounts - Adhesive Backed

Material: Nylon 6.6

Color: White

UL Recognized: E136577

Height (In.):	.25
Height (mm):	6.4
Length (In.):	1.50
Length (mm):	38.1
Width (In.):	1.50
Width (mm):	38.1
Adhesive Type:	Rubber
CE Compliant:	CT-ACC1 / 10.96
Environment:	Indoors
Max. Static Load (g):	513
Max. Static Load (Lbs.):	1.13
Metric Screw Size:	M3
Mounting Method:	Adhesive Backed
Screw Size:	#6 (M3)
Std. Pkg. UOM:	PK
Used With Cable Ties:	M, I, S, HS, LH, H & HLM
UOM:	PC
Std. Pkg. Qty.:	50
Min. Order Qty.:	50

