



3M™ Fastener Hook & Loop SJ352B, Black, 25 mm x 1.25 m, 4.4 mm, Blister IPC

Part Number SJ352B, White, 1.25M X 25MM

Part Number SJ352B, Black, 1.25M X 25MM



3M™ Hook & Loop Fastener, SJ352B, white



- High performance rubber based adhesive designed for indoor applications requiring medium temperature resistance
- Provides a firm adhesive bond to a wide variety of surfaces
- Woven nylon is durable for thousands of closures
- Quick fastening that helps reduce production time and costs

Product Details

3M™ Hook and Loop fastener SJ3520 is our white, high performance PSA nylon hook and loop with a rubber adhesive and white polypropylene film liner. It provides a firm adhesive bond to a wide variety of surfaces including many low surface energy plastics and powder coats. It's designed for indoor use and has an engaged thickness of 4.4 mm.

3M™ Hook and Loop fastener SJ3520 is coated with a high performance rubber adhesive and offers a medium temperature performance up to +50 °C long-term (+70 °C short-term). Our white nylon hook and loops are designed for indoor use and bond well to paper and cardboard, paint, bare and painted metal, glass, sealed wood, and many plastics.

- High performance rubber based adhesive designed for indoor applications requiring medium temperature resistance
- Provides a firm adhesive bond to a wide variety of surfaces
- Woven nylon is durable for thousands of closures
- Quick fastening that helps reduce production time and costs
- Suitable for a wide range of industries such as transportation, electronics, office equipment, shop fitting and both internal and external signals

Specifications

| | |
|---|----------------------------------|
| Adhesive Type | High Performance Rubber Adhesive |
| Overall Width (Metric) | 25 mm |
| Pack Quantity | 4 |
| Product Color | Black ,white |
| Smallest Saleable Unit | Roll |
| Total Tape Thickness without Liner (metric) | 2.4 mm |