



**3M™ Dual Lock™ Reclosable Fastener Twin Pack
SJ354X, Black, 25 mm x 5 m, 5.7 mm, Twin Pack
Squares**

Part Number SJ354X, Black, 5M X 25MM



- Reclosable fastening system - up to 12 times stronger than traditional hook & loop technology
- Fast assembly with no drilling
- TM®InvisibleTM® fixing
- High temperature and solvent resistance

Details

- Reclosable fastening system - up to 12 times stronger than traditional hook & loop technology
- Fast assembly with no drilling
- TM®InvisibleTM® fixing
- High temperature and solvent resistance
- Mini strips for smaller jobs and testing
- Re-sealable

3MTM Dual LockTM Reclosable Fastener SJ3540 has a rubber based adhesive on the back of a black, polypropylene reclosable fastener. It's suitable for bonding many plastics, powder coated paints and other low surface energy materials. Our reclosable fastener has 40 mushroom shaped stems / cm² with a 5.8 mm engaged thickness.

Attach a variety of materials with 3MTM Dual LockTM Reclosable Fastener SJ3540. Our fastener is designed to bond many plastics, powder coated paints and other low surface energy materials with its interlocking mushroom shaped stems. It's a Type 250 stem density polyolefin fastener that is backed with a rubber based pressure sensitive adhesive and has 250 stems per square inch. Our fastener has closure action life of 1000 times before losing 50% of its original strength, making it reliable, for longer.

Suggested Applications

- Apply to plastics, powder coated paints and other low surface energy materials
- Interior signage
- Decorative trim
- Office partitions
- Graphic attachment
- Access panels
- Specialty vehicles (interior attachments)
- L-bracket edging, repositionable shelving
- Hang signage