

# PC 121208



Sample image

**Order symbol:** PC 121208

**Product nbr:** 7032670

UL Code: 7042670

UL Name: UL PC 121208

**Description:** Enclosure. PC


**Remarks:** Opaque cover

**EAN:** 6418074058393

**El. number:**

- Finland: 3435358
- Denmark: 8212002720
- Sweden: 2536120

**Including:** Base with screws for mounting plate/DIN-rail. cover with PUR gasket and stainless steel cover screws.



Dimensions:	Height	Width	Depth
mm:	120	122	75
inch:	4.72	4.8	2.95

**Materials:**

Material: Polycarbonate  
Base colour: RAL 7035 -light grey

**Accessories:**

- TRH 1212 DIN-15 Mounting rail. for enclosures: (110 x 35 x 1)
- TRM 0812 DIN-15 Mounting rail. for enclosures: (106 x 15 x 1)
- TRM 1212 DIN-15 Mounting rail. for enclosures: (110 x 15 x 1)
- TF 28037 Mounting foot kit (4 pcs). for enclosures:
- TM 1212 Back Panel. for enclosures: (96 x 111 x 1)

Cover colour: RAL 7035 -light grey

Gasket material: Polyurethane

TH A

Gray plastic hinges (2 pcs)

**Temperatures:**

Temperature °C (short term):: -40 ... 120

Temperature °C (continuous): -40 ... 80

Temperature °F (short term): -40 ... 250

Temperature °F (continuous): -40 ... 175

**Rating:**

Ingress protection (EN 60529):	IP66; IP67;
Impact Resistance (EN 62262):	IK07; IK08;
Electrical insulation:	Totally insulated
Halogen free (DIN/VDE 0472, Part 815):	1
UV resistance:	UL 508
Flammability Rating:	UL 746C 5"
Glow Wire Test (IEC 695-2-1) °C:	960 °C
NEMA Class	

**Certificates:**

SGSFimko\_EURONORD