



inch: 5.91 13.39 4.72

**Materials:**

Material: Polycarbonate  
Base colour: RAL 7035 -light grey  
Cover colour: RAL 7035 -light grey  
Gasket material: Polyurethane

**Temperatures:**

Temperature °C (short term):: -40 ... 120  
Temperature °C (continuous): -40 ... 80  
Temperature °F (short term): -40 ... 250  
Temperature °F (continuous): -40 ... 175

(307 x 35 x 1)

TF 28037 Mounting foot kit (4 pcs). for enclosures:  
TRH 15 DIN-15 Mounting rail. for enclosures:  
(122 x 35 x 1)  
TM 1534 Back Panel. for enclosures:  
(303 x 136 x 1)  
TH A Gray plastic hinges (2 pcs)

**Rating:**

Ingress protection (EN 60529): IP66; IP67;  
Impact Resistance (EN 62262): IK07; IK08;  
Electrical insulation: Totally insulated  
Halogen free (DIN/VDE 0472, Part 815): 1  
UV resistance: UL 508  
Flammability Rating: UL 746C 5"  
Glow Wire Test (IEC 695-2-1) °C: 960 °C  
NEMA Class

**Certificates:**

SGSFimko\_EURONORD