

# PC 162409



Sample image

**Order symbol:** PC 162409

**Product nbr:** 7032810

**Description:** Enclosure. PC


**Remarks:** Opaque cover

**EAN:** 6418074058461

**El. number:**

- Finland: 3435372
- Denmark: 8212002924
- Sweden: 2536128

**Including:** Base with screws for mounting plate/DIN-rail. cover with PUR gasket and stainless steel cover screws.



Dimensions:	Height	Width	Depth
mm:	164	244	90
inch:	6.46	9.61	3.54

## Materials:

Material:	Polycarbonate
Base colour:	RAL 7035 -light grey
Cover colour:	RAL 7035 -light grey

## Accessories:

TRH 24	DIN-15 Mounting rail. for enclosures: (226 x 35 x 1)
TF 28037	Mounting foot kit (4 pcs). for enclosures:
MIN 20	DIN-15 Mounting rail. for enclosures: (225 x 15 x 1)
TM 1624	Back Panel. for enclosures: (212 x 151 x 1)
TH A	Gray plastic hinges (2 pcs)

Gasket material: Polyurethane

**Temperatures:**

Temperature °C (short term):: -40 ... 120

Temperature °C (continuous): -40 ... 80

Temperature °F (short term): -40 ... 250

Temperature °F (continuous): -40 ... 175

**Rating:**

Ingress protection (EN 60529): IP66; IP67;

Impact Resistance (EN 62262): IK07; IK08;

Electrical insulation: Totally insulated

Halogen free (DIN/VDE 0472, Part 815): 1

UV resistance: UL 508

Flammability Rating: UL 746C 5"

Glow Wire Test (IEC 695-2-1) °C: 960 °C

NEMA Class

**Certificates:**

SGSFimko\_EURONORD