


# TM 1212



Sample image

**Order symbol:** TM 1212

**Product nbr:** 9512014

**Description:** Back Panel. for enclosures:

**Remarks:** 122x120x65. 122x120x105

**Including:**

**EAN:** 6418074034021

**El. number:**

- Finland: 3423923
- Denmark: 8212003949
- Sweden: 2536157

TM\_0808,1212

<b>Dimensions:</b>	<b>Height</b>	<b>Width</b>	<b>Depth</b>
mm:	96	111	1
inch:	3.78	4.37	0.04

**Materials:**

Material:

Base colour:

Cover colour:

Gasket material:

**Rating:**

Ingress protection (EN 60529):

Impact Resistance (EN 62262):

Electrical insulation: Not insulated

Halogen free (DIN/VDE 0472, Part 815): 0

UV resistance: -

Flammability Rating:

Glow Wire Test (IEC 695-2-1) °C: C

NEMA Class

**Temperatures:**

Temperature °C (short term)::

Temperature °C (continuous):

Temperature °F (short term):

Temperature °F (continuous):

**Certificates:**