

## IN 19 4

### Screwdriver bit socket 1/2"

for in-hex screws

Code	ETIM
6153070	ECO02157 Innensechskant-Einsatz für Steckschlüssel
EAN	UNSPSC
4010886615300	27-11-17-01 Schraubendreher
Country of Origin	eCl@ss
Germany	21-04-04-02 Schraubendrehereinsatz
Customs tariff no.	
82079030	



### Article description

- Square drive as per DIN 3120 - C 12.5, ISO 1174, with ball retaining groove
- Hand-operated, knurled grip
- Chrome-plated
- With pressed-in pin in GEDORE vanadium special steel, manganese-phosphated
- IN 19 17 for oil filter and drain plug screws
- \* not standardised

### Article information

Contents (Qty of pieces)	1 tlg.	Drive connector square female (metric)	12,5 mm
Total length [mm]	61 mm	Total width [mm]	23 mm
Total height [mm]	23 mm	Drive connector square female [inch]	1/2"
Net weight [kg]	0,068 kg	Working length	38,0 mm
Material	Chrome-vanadium steel	Tip length	22,0 mm
Width across flats 1 [mm]	4	Standard	not standardised
Surface	chrome-plated	Insert Ø Actuator	22,5 mm
REACH registration available	0		