



AURELIA® ROBUST

4.5mil, Nitrile Powder Free Examination Gloves

AURELIA® GLOVES

A SUPERMAX HEALTHCARE BRAND

sales@supermax.co.uk

+441733 615215

Supermax Healthcare Ltd,

Unit 12-16 Titan Drive

Fengate, Peterborough

PE1 5XN

aureliagloves.co.uk



Regulations	PPE Regulation (EU) 2016/425 Medical Device Regulation (EU) 2017/745, 93/42/EEC
Quality Standards	ISO 9001:2015 Quality Management Systems ISO 13485: 2016 Medical Devices Quality Management Systems
Harmonised Standards	BS EN ISO 374 - 1,2,4,5 Protective gloves against dangerous chemicals and microorganisms. BS EN 455 1-4 Medical gloves for single use. EN 420: 2003 + A1: 2009 Protective gloves. General requirements and test methods. BS EN 1184: 1997. Materials and articles in contact with foodstuffs.



XS	S	M	L	XL	XXL
93895	93896	93897	93898	93899	93890

Sizes & Dimensions	Single wall thickness	Physical Properties												
<p>XS 70+10 mm S 80+10 mm M 95+10 mm L 110+10 mm XL > 110 mm</p>	<p>min. 240 mm</p> <p>① min. 0.13 mm ② min. 0.09 mm ③ min. 0.05 mm</p>	<table border="1"> <thead> <tr> <th></th> <th>Unaged</th> <th>Aged</th> </tr> </thead> <tbody> <tr> <td>Tensile Strength</td> <td>Min. 14.0 MPa</td> <td>Min. 14.0 MPa</td> </tr> <tr> <td>Elongation</td> <td>Min. 500%</td> <td>Min. 400%</td> </tr> <tr> <td>Strength at Break</td> <td>Min. 6N</td> <td>Min. 6N</td> </tr> </tbody> </table>		Unaged	Aged	Tensile Strength	Min. 14.0 MPa	Min. 14.0 MPa	Elongation	Min. 500%	Min. 400%	Strength at Break	Min. 6N	Min. 6N
	Unaged	Aged												
Tensile Strength	Min. 14.0 MPa	Min. 14.0 MPa												
Elongation	Min. 500%	Min. 400%												
Strength at Break	Min. 6N	Min. 6N												



Nitrile



Powder Free



5 Years



Textured



5.0g +/- 0.2g



Sky Blue

