



Features

- 1200 W POWER
- 260 ML EASY-TO-FILL WATER TANK
- FAST HEAT-UP TIME - 45-50 SECONDS
- 12-15 MINUTES OF CONTINUOUS STEAM
- COMPACT FOR EASY STORAGE
- 1.9 M POWER CORD
- INCLUDES 2 IN 1 FABRIC AND LINT BRUSH AND MEASURING JUG



Shipping Details / Product Details

Carton Qty: 6
 Container Qty:
 20 Ft: 3522
 40 Ft: 7260
 40 HQ: 8640
 Carton Details: 40.50l x 32.00w x 36.50h cm
 CBM: 0.05
 Carton Weight Net: 7.13 kg
 Carton Weight Gross: 7.57 kg
 Port: NINGBO

Product Code: BEL0815
 Packaging Type: Closed Colour Box
 Box Size: 30.50l x 13.00w x 17.00h cm
 Product Size: 13.00l x 11.00w x 28.00h cm
 MOQ: 2000
 Barcode: 5054061102413
 TUC: 05054061102420
 Commodity Code: 8516 7970 90
 Duty: 2.70%

OFFER VALID FOR 14 DAYS

PRICE: £15.00
RRP: £49.99

Important:

The unit prices quoted on this document includes certification of the product to ensure compliance with mandatory UK and European legislation. Please note: Any optional non-mandatory testing is not included in the quoted price. Any optional testing requirements, and subsequent cost revisions, must be agreed prior to an order being placed. Any optional testing requested after the order is placed will not be funded by Ultimate Products.

UP Global Sourcing T/A Ultimate Products

Unless otherwise agreed and confirmed in writing, this offer is subject to the standard terms and conditions of Ultimate Products. These are available at www.upgs.com/terms. Retail price provided for information only; retailers are free to set their own retail prices.

Ultimate Products UK Ltd.,
 Manor Mill, Manchester OL9 0DD, UK.
 Tel: +44 (0)161 627 1400 Fax: +44 (0)161 628 2126
sales@upgs.com www.upgs.com

