



Features

- 1500 W POWER
- READY TO USE IN 30 SECONDS
- UP TO 15 MINUTES OF CONTINUOUS STEAM
- 270 ML REMOVABLE WATER TANK
- ANTI-CALC FILTER
- 1.9 M POWER CORD
- 2 STEAM SETTINGS
- COMPACT FOR EASY STORAGE
- INCLUDES FABRIC BRUSH AND MEASURING CUP

Beldray^{est 1872}
**HANDI STEAM
MAX PRO**
-- ROSE GOLD --
SPECIAL EDITION



Multipurpose, vertical garment steamer

- Perfect for all fabric types and clothing



3 YEAR WARRANTY

Beldray^{est 1872}
**HANDI STEAM
MAX PRO**
-- ROSE GOLD --
SPECIAL EDITION



Shipping Details / Product Details

Carton Qty: 6
Container Qty:
20 Ft: 3034
40 Ft: 6674
40 HQ: 7888
Carton Details: 43.00l x 36.50w x 33.00h cm
CBM: 0.05
Carton Weight Net: 7.24 kg
Carton Weight Gross: 7.90 kg
Port: XIAMEN

Product Code: BEL0932RG
Packaging Type: Closed Colour Box
Box Size: 13.50l x 17.00w x 34.00h cm
Product Size: 18.70l x 11.90w x 29.20h cm
MOQ: 3034
Barcode: 5054061103991
TUC: 05054061104004
Commodity Code: 8516 7970 90
Duty: 2.20%

FREE STOCK: 53
OFFER VALID FOR 14 DAYS

PRICE: £15.00
RRP: £49.99

Important:

The unit prices quoted on this document includes certification of the product to ensure compliance with mandatory UK and European legislation. Please note: Any optional non-mandatory testing is not included in the quoted price. Any optional testing requirements, and subsequent cost revisions, must be agreed prior to an order being placed. Any optional testing requested after the order is placed will not be funded by Ultimate Products.

UP Global Sourcing T/A Ultimate Products

Unless otherwise agreed and confirmed in writing, this offer is subject to the standard terms and conditions of Ultimate Products. These are available at www.upgs.com/terms. Retail price provided for information only; retailers are free to set their own retail prices.

Ultimate Products UK Ltd.,
Manor Mill, Manchester OL9 0DD, UK.
Tel: +44 (0)161 627 1400 Fax: +44 (0)161 628 2126
sales@upgs.com www.upgs.com

