



## Shipping Details / Product Details

Carton Qty:	2
Container Qty:	20 Ft: 1020 40 Ft: 1998 40 HQ: 2386
Carton Details:	45.50l x 42.50w x 31.50h cm CBM: 0.06
Carton Weight Net:	6.00 kg
Carton Weight Gross:	6.70 kg
Port:	NINGBO
Product Code:	BEL01137
Packaging Type:	Closed Colour Box
Box Size:	21.60l x 40.50w x 28.60h cm
Product Size:	35.40l x 19.10w x 25.30h cm MOQ: 1020
Barcode:	5054061103977
TUC:	05054061109757
Commodity Code:	8516 4000 00
Duty:	2.70%

**OFFER VALID FOR 14 DAYS**

**PRICE: £28.75**

**RRP: £79.99**

## Features

- 2400 W POWER
- 1.2 L REMOVABLE WATER TANK
- CERAMIC SOLEPLATE
- ANTI-CALC FUNCTION
- ANTI-DRIP TO KEEP FABRIC SPOTLESS
- BUILT-IN CORD STORAGE
- 2 M POWER CORD

### Important:

The unit prices quoted on this document includes certification of the product to ensure compliance with mandatory UK and European legislation. Please note: Any optional non-mandatory testing is not included in the quoted price. Any optional testing requirements, and subsequent cost revisions, must be agreed prior to an order being placed. Any optional testing requested after the order is placed will not be funded by Ultimate Products.

### UP Global Sourcing T/A Ultimate Products

Unless otherwise agreed and confirmed in writing, this offer is subject to the standard terms and conditions of Ultimate Products. These are available at [www.upgs.com/terms](http://www.upgs.com/terms). Retail price provided for information only: retailers are free to set their own retail prices.

Ultimate Products UK Ltd.,  
Manor Mill, Manchester OL9 0DD, UK.  
Tel: +44 (0)161 627 1400 Fax: +44 (0)161 628 2126  
[sales@upgs.com](mailto:sales@upgs.com) [www.upgs.com](http://www.upgs.com)

