



Supplier of Industrial and Consumer Batteries, Chargers, and Battery

JOIN OUR NEWSLETTER



SEARCH



BROWSE BY
**PRODUCT
CATEGORY**



BROWSE BY
**DEVICE
MANUFACTURER**



ADVANCED
**INDUSTRY
SEARCH**

Search by keyword, part #, catalog #, manufacturer...

Search only Dantona part numbers

SEARCH

[Home](#) / [TOOL-224](#)



hover to zoom; click to enlarge

PART#: TOOL-224

Chemistry: Nickel Cadmium (NICD)
Voltage: 19.2
Capacity: 2000mAh
Measurements: 5.4" x 3.1" x 4.4"
 137.16mm x 78.74mm x 111.76mm

[Find a Distributor](#)

This replacement 14.4 Volt 3300 mAh Nickel Metal Hydride Battery is used in Lincoln Power Tools and meets or exceeds original manufacturer specifications.

SPECIFICATIONS

Shipping Weight (oz)	36.0000
Manufacturer	Dantona
Warranty	6
UPC	728286022249
Length	5.4" (137.16mm)
Width	3.1" (78.74mm)
Height / Diameter	4.4" (111.76mm)
26.4	19.2
mAh	2000
Number of Cells	16
Battery Chemistry	Nickel Cadmium (NICD)
Rechargeable	Rechargeable
Battery Color	Black
Qty Per Package	1

Compatible Batteries and Devices

- [Batteries \(5\)](#)
- [Devices \(4\)](#)

Type of Cell	Cylindrical, Sub-C
Weight	36 oz



IMAGES ARE FOR REFERENCE ONLY! Please note that the capacity (mAh) may change without notice. Always consult the product specifications for correct information. Dantona Industries, Inc. is not affiliated in any way with any of the manufacturers listed in this catalog and the batteries sold in this catalog have not been sponsored or approved by any of such manufacturers. Any trademarks or model numbers listed in this catalog are identified for compatibility or cross-reference purposes only.

**CAN'T FIND
THE BATTERY
YOU NEED?**

**CALL US AT
1-800-Dantona
TO SPEAK TO
A BATTERY EXPERT**



**VIEW OUR WIDE
SELECTION OF**

**Custom
Battery
Packs**

SHOP OUR CUSTOM PACKS

[Sitemap](#)

[FAQ](#)

[Custom Battery Pack Ordering Guide](#)

[Contact Us](#)

[Privacy Policy](#)

© 2022 Dantona Industries Inc.®

Parse error: syntax error, unexpected '[' in /chroot/home/dantonac/dantona.com/html/media/wysiwyg/MfHqA.jpg on line 9