

PSSu BP 1/8 C

312601



PSSu, base module for electronic modules, periphery, 1-row, 4 connection levels, 8 terminals, spring-loaded connection.

## Technical details

### General data

Approval: CE, BG, cULus Listed, TÜV

Application range: Standard/failsafe

### Technical data

#### Environmental data

Humidity rating: 93 % r. h. at 40 °C

#### Mechanical data

Housing material lower section: PA

Housing material upper part: PC

Connection terminal: Cage clamp terminal

Terminal style: fixed

Height dimension: 129 mm

Width dimension: 12.6 mm

Net weight: 37 g

Gross weight: 49 g

#### Environment

RoHS directive: 2011/65/EU, 2015/863/EU


RoHS conformity: yes

RoHS exceptions: yes

RoHS except.s acc. to direct.: 6c


REACH compliance:	contains min. 1 SVHC-substance
REACH included substances:	Lead
%-part of the pollutant:	> 0,1%
CAS No.:	7439-92-1
WEEE klassifikation (08/2018):	5 devices (feed size < 50cm)
<b>Commercial data</b>	
ECLASS version:	ECLASS-9.1
ECLASS Reference Feature:	27242603
ETIM Version:	ETIM-7.0
ETIM Reference Group:	EG000024

## Optional accessories



312960

PSSu A LA2 ( 10x50 pcs.)




312962

PSSu A LA4 (10x50 pcs.)



312951

PSSu A ME1 (10x6 pcs.)



312961

PSSu A LA3 (10x50 pcs.)



312950

PSSu A ME0 (10x6 pcs.)



312953

PSSu A ME3 (10x6 pcs.)



312964

PSSu A SH T (10 pcs.)



312952

PSSu A ME2 (10x6 pcs.)



312963

PSSu A SH S (10 pcs.)



312955

PSSu A ME5 (10x6 pcs.)




312900

PSSu A ET (10 pcs.)



312954

PSSu A ME4 (10x6 pcs.)



312957

PSSu A ME7 (10x6 pcs.)



312902

PSSu A EC



312956

PSSu A ME5 (10x6 pcs.)



312967

PSSu A LA0.1 (10 x 108 pcs.)



312901

PSSu A ETM (2 pcs.)



312959

PSSu A LA1 (10x50 pcs.)



312958

PSSu A LA0 (10 x 108 pcs.)



312949

PSSu A ET PE (10 pcs.)