



24" HD LED Digital TV with Built-in Satellite Tuner

- 24" HD Ready widescreen LED TV
- Built-in Freeview HD and Digital Freeview Channels
- Built-in Satellite Tuner
- HDMI input for your external devices and consoles
- Can be wall mounted (200mm x 100mm)

	EAN	5060062269796
Specifications	Model No.	C2420S
	Chipset	MSD3663
	Sales Market	UK
	VESA Size	200 x 100
	Wall Mount Screws	M4 x 8
	Speaker Output	2 x 3W
	Actual Size of Display (Diagonal)	23.6"

Display	Display Type	LED
	Resolution	1366 x 768 (16:9)
	Brightness (nit)	180
	Contrast	3000:1
	Display Colours	16.7M
	Refresh Rate	60Hz
	Viewing Angle H/V	178/178
	Reponse Time	14ms

Accessories	Remote	1
	Battery	AAA x 2
	User manual	N/A

Terminals		
	HDMI Input	1
	USB	1
	RCA Component + AUDIO Input	1
	RCA Composite + AUDIO Input	1
	15-PIN VGA + AUDIO Input	1
	RF Input	1
	Optical Digital AUDIO output	1
	3.5mm Headphone Output	1

Features		
	DVD	No
	DVB-S	With
	DVB-S2	With
	DVB-T+C	With
	DVB-T2+C	With
	CI	With
	3D Digital Comb Filter + 3D Noise Reduction	Yes
	Automatic Volume Control	Yes
	Sleep Timer	Yes
	NO Signal Shut Down	Yes
	Adjustable Bass & Treble Controls	Yes
	Adjustable Balance Control	Yes
	Picture Modes	Standard/Dynamic/Soft/User
	Preset Sound Modes	Standard/Music/Movie/User
	OSD Menu Language	English/French/Spanish/Italy/Germany/Portugal
	Aspect Ratio Modes	Wide/Zoom/Cinema/Normal
	PVR Function	Recording standby, time-shift EPG recording reservation

Power		
	Power Supply	AC 100V-240V 50 Hz/60Hz
	Operation power consumption	24W
	KWh/annum	36kWh
	Standby Consumption	<0.5W
	Energy class	A

Dimension		
	Unit Dimensions w Stand	550 x 153 x 354
	Unit Dimensions w/o Stand	550 x 78 x 332
	Carton Box Dimensions	2.3