

Product data sheet

Specifications



Wall-Mounted Open Box 12U W600 D400 Fixed 19" Glazed Door R7035

NSYOPB12U4F

Main

| | |
|-----------------------------|---|
| Range | Actassi |
| Product name | Actassi OPB |
| Product or component type | 19" enclosure |
| Device application | Cabling |
| Applications | To protect network connectivity equipment To mount 19" equipment |
| Enclosure type | Open box |
| Support equipment | 2 x fixed 19" uprights recessed of 120 mm from the front (pitch 25 mm) |
| Front face | Glazed door |
| Door type | Front glazed door - with 1 point locking system (key: 333) - reversible opening at 180 ° |
| Accessibility for operation | Side Rear Front |
| Removable parts | Front door removable toolless Top blanking plate Bottom blanking plate Rear blanking plate Side panels removable toolless |
| Colour | Light grey (RAL 7035) |

Complementary

| | |
|--------------------|---|
| Device composition | 3 x cable entries 1 x glazed door front 2 x panels side 2 x 19" uprights front 1 x open structure |
| Load rating | 50 kg static 3 kg by unit |
| Back face | Cut-out |
| Side face | Panel |
| Number of cut-out | 1 cut-outside 1 cut-outbottom 1 cut-outtop |
| Installation mode | Wall mounted |
| Material | Sheet steel: structure Sheet steel: door Sekurit glass: door Galvanized steel: upright |

| | |
|---------------------|------------------------|
| Surface finish | Epoxy-polyester powder |
| Width | 600 mm |
| Height | 650 mm |
| Depth | 400 mm |
| Net weight | 23 kg |
| Number of rack unit | 12U |
| Targeted region | Europe |

Environment

| | |
|-------------------------|------------------------------|
| IK degree of protection | IK08 conforming to IEC 62262 |
| IP degree of protection | IP20 conforming to IEC 60529 |
| Standards | EIA-310D IEC 60297-3-100 |

Packing Units

| | |
|------------------------------|----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Weight | 21.0 kg |
| Package 1 Height | 44.5 cm |
| Package 1 width | 62.0 cm |
| Package 1 Length | 70.0 cm |
| Unit Type of Package 2 | PAM |
| Number of Units in Package 2 | 6 |
| Package 2 Weight | 144.0 kg |
| Package 2 Height | 154.0 cm |
| Package 2 width | 100.0 cm |
| Package 2 Length | 120.0 cm |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | Product Environmental Profile |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|