

Product data sheet

Specifications



Actassi KDB - Wall-Mounted KD Box 15U D600 F 19" Glazed

NSYKDB15U6F

Main

Range	Actassi
Product name	Actassi KDB
Product or component type	19" enclosure
Device application	Cabling
Applications	To mount 19" equipment To protect network connectivity equipment
Enclosure type	Knock down box
Support equipment	2 x 19" uprights recessed of 120 mm from the front (pitch 25 mm)
Front face	Glazed door
Door type	Front glazed door - with key lock (key: 333) - reversible opening at 180 °
Accessibility for operation	Rear Front
Removable parts	Front door removable toolless
Colour	Light grey (RAL 7035)

Complementary

Device composition	3 x cable entries 1 x glazed door front 2 x panels side 2 x 19" uprights front 1 x dismantable structure
Load rating	50 kg static 3 kg by unit
Back face	Cut-out
Side face	Panel
Number of cut-out	1 cut-outside 19" knock down entry cable: top and bottom 19" knock down entry fan plate: top and bottom
Installation mode	Wall mounted
Material	Sheet steel: structure Sheet steel: door Sekurit glass: door Sheet steel: 19" upright
Surface finish	Epoxy-polyester powder
Width	600 mm
Height	751.8 mm

Depth	600 mm
Net weight	25.96 kg
Number of rack unit	15U
Targeted region	Europe

Environment

IK degree of protection	IK08 conforming to IEC 62262
IP degree of protection	IP20 conforming to IEC 60529
Standards	IEC 60297-3-100 EIA-310E

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	25.96 kg
Package 1 Height	77.0 cm
Package 1 width	62.5 cm
Package 1 Length	23.0 cm

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information

Contractual warranty

Warranty	18 months
----------	-----------