

# Product data sheet

Specifications



## Wall-Mounted Open Box 9U W600 D400 Fixed 19" Plain Door R7035

NSYOPB9U4FR

### Main

<b>Range</b>	Actassi
<b>Product name</b>	Actassi OPB
<b>Product or component type</b>	19" enclosure
<b>Device application</b>	Cabling
<b>Applications</b>	To mount 19" equipment To improve security of the equipment To protect network connectivity equipment
<b>Enclosure type</b>	Open box
<b>Support equipment</b>	2 x fixed 19" uprights recessed of 120 mm from the front (pitch 25 mm)
<b>Front face</b>	Plain door
<b>Door type</b>	Front plain door - with 1 point locking system (key: 333) - reversible opening at 180 °
<b>Accessibility for operation</b>	Rear Front Side
<b>Removable parts</b>	Front door removable toolless Top blanking plate Bottom blanking plate Rear blanking plate Side panels removable toolless
<b>Colour</b>	Light grey (RAL 7035)

### Complementary

<b>Device composition</b>	3 x cable entries 2 x panels side 2 x 19" uprights front 1 x open structure 1 x plain door front
<b>Load rating</b>	50 kg static 3 kg by unit
<b>Back face</b>	Cut-out
<b>Side face</b>	Panel
<b>Number of cut-out</b>	1 cut-outside 1 cut-outbottom 1 cut-outtop
<b>Installation mode</b>	Wall mounted
<b>Material</b>	Sheet steel: structure Sheet steel: door Galvanized steel: upright

Surface finish	Epoxy-polyester powder
Width	600 mm
Height	515 mm
Depth	400 mm
Net weight	18.66 kg
Number of rack unit	9U
Targeted region	Europe

## Environment

IK degree of protection	IK10 conforming to IEC 62262
IP degree of protection	IP20 conforming to IEC 60529
Standards	EIA-310D IEC 60297-3-100

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	18.44 kg
Package 1 Height	47.0 cm
Package 1 width	57.0 cm
Package 1 Length	61.0 cm
Unit Type of Package 2	PAM
Number of Units in Package 2	9
Package 2 Weight	179.0 kg
Package 2 Height	187.0 cm
Package 2 width	100.0 cm
Package 2 Length	120.0 cm

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information

## Contractual warranty

Warranty	18 months
----------	-----------