

# Product datasheet

Specifications

## Actassi - 1 x fan - thermal management - with led switch



NSY1FAN230T

### Main

Range of product	Actassi
Product or component type	19" fan plate
Accessory / separate part category	Thermal management
Device application	Ventilation
Provided equipment	Blanking plate Led switch Without cable
Colour	Light grey (RAL 7035)
Air flow	90 ft3/h 152 m3/h

### Complementary

Range compatibility	Actassi KDB
Device composition	1 fan
Function available	Thermostat
Material	Sheet steel painted
Mounting location	Bottom of enclosure Front of enclosure Top of enclosure
Fixing mode	Cage nut: M6
Electrical connection	Wires terminal block
Height	132 mm
Width	486 mm
Depth	52 mm
Net weight	2.038 kg

### Environment

Ambient air temperature for operation	0...55 °C
Noise level	42 dB

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	2.038 kg
Package 1 Height	7.0 cm
Package 1 width	15.5 cm
Package 1 Length	50.0 cm
Unit Type of Package 2	P12
Number of Units in Package 2	54
Package 2 Weight	124.0 kg
Package 2 Height	55.0 cm
Package 2 width	80.0 cm
Package 2 Length	120.0 cm

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information

## Contractual warranty

Warranty	18 months
----------	-----------