

## Datasheet

### PFA Insulated Flat Pair Thermocouple Cable



- Single pair of PFA insulated conductors, laid flat with PFA jacket
- Good mechanical strength and flexibility, resistant to oils, acids and other adverse fluids
- Tolerance Class 1 for optimum accuracy
- Insulation rating -75°C to 260°C
- Colour code (cores & jacket) to IEC-584-3

| Type | Conductors | Reel Length | Manufacturers Code | Order Code                  |
|------|------------|-------------|--------------------|-----------------------------|
| E    | 7/0.2mm    | 10m         | WE-250-D           | <a href="#">XF-1593-FAR</a> |
| E    | 7/0.2mm    | 25m         | WE-250-D           | <a href="#">XF-1594-FAR</a> |
| E    | 7/0.2mm    | 50m         | WE-250-D           | <a href="#">XF-1595-FAR</a> |
| E    | 7/0.2mm    | 100m        | WE-250-D           | <a href="#">XF-1596-FAR</a> |
| J    | 7/0.2mm    | 10m         | WJ-248-D           | <a href="#">XF-1305-FAR</a> |
| J    | 7/0.2mm    | 25m         | WJ-248-D           | <a href="#">XF-571-FAR</a>  |
| J    | 7/0.2mm    | 50m         | WJ-248-D           | <a href="#">XF-572-FAR</a>  |
| J    | 7/0.2mm    | 100m        | WJ-248-D           | <a href="#">XF-1294-FAR</a> |
| K    | 1/0.2mm    | 25m         | WK-609-D           | <a href="#">XF-1677-FAR</a> |
| K    | 1/0.2mm    | 100m        | WK-609-D           | <a href="#">XF-1678-FAR</a> |
| K    | 1/0.3mm    | 10m         | WK-356-D           | <a href="#">XF-1291-FAR</a> |
| K    | 1/0.3mm    | 25m         | WK-356-D           | <a href="#">XF-573-FAR</a>  |
| K    | 1/0.3mm    | 50m         | WK-356-D           | <a href="#">XF-1310-FAR</a> |
| K    | 1/0.3mm    | 100m        | WK-356-D           | <a href="#">XF-1276-FAR</a> |
| K    | 1/0.508mm  | 25m         | WK-306-D           | <a href="#">XF-1260-FAR</a> |
| K    | 1/0.508mm  | 50m         | WK-306-D           | <a href="#">XF-1252-FAR</a> |
| K    | 1/0.508mm  | 100m        | WK-306-D           | <a href="#">XF-1779-FAR</a> |
| K    | 7/0.2mm    | 10m         | XS-751-D           | <a href="#">XF-1309-FAR</a> |
| K    | 7/0.2mm    | 25m         | XS-751-D           | <a href="#">XF-574-FAR</a>  |
| K    | 7/0.2mm    | 50m         | XS-751-D           | <a href="#">XF-575-FAR</a>  |
| K    | 7/0.2mm    | 100m        | XS-751-D           | <a href="#">XF-576-FAR</a>  |
| N    | 7/0.2mm    | 25m         | WN-121-D           | <a href="#">XF-581-FAR</a>  |
| T    | 1/0.3mm    | 25m         | WT-203-D           | <a href="#">XF-577-FAR</a>  |
| T    | 1/0.3mm    | 50m         | WT-203-D           | <a href="#">XF-1761-FAR</a> |
| T    | 1/0.5mm    | 10m         | WT-309-D           | <a href="#">XF-1707-FAR</a> |
| T    | 1/0.5mm    | 25m         | WT-309-D           | <a href="#">XF-1705-FAR</a> |
| T    | 1/0.5mm    | 50m         | WT-309-D           | <a href="#">XF-1706-FAR</a> |
| T    | 1/0.5mm    | 100m        | WT-309-D           | <a href="#">XF-1708-FAR</a> |
| T    | 7/0.2mm    | 25m         | WT-305-D           | <a href="#">XF-578-FAR</a>  |
| T    | 7/0.2mm    | 50m         | WT-305-D           | <a href="#">XF-579-FAR</a>  |
| T    | 7/0.2mm    | 100m        | WT-305-D           | <a href="#">XF-580-FAR</a>  |