


Datasheet

IEC Glassfibre Insulated Flat Pair Thermocouple Extension Cable



- Glassfibre insulated extension cable in thermocouple types; K, J or N
- Glassfibre insulated flat pair construction, conductors laid flat, Glassfibre insulated with Glassfibre overall, silicone varnished throughout
- Good temperature resistance but not suitable where fluids are present
- All types; conductors are made from associated K, J or N thermocouple alloy type
- Tolerance Class 2 to IEC-584
- Insulation rating -60°C to 350°C (short periods up to 400°C)
- Colour code (cores & jacket) to IEC-584-3

Type	Conductors	Reel Length	Manufacturers Code	Order Code
J	1/0.2mm	10m	WJ-229-D	XF-1602-FAR
J	1/0.2mm	25m	WJ-229-D	XF-1600-FAR
J	1/0.2mm	50m	WJ-229-D	XF-1603-FAR
J	1/0.2mm	100m	WJ-229-D	XF-1604-FAR
J	1/0.315mm	10m	WJ-230-D	XF-1605-FAR
J	1/0.315mm	25m	WJ-230-D	XF-1606-FAR
J	1/0.315mm	50m	WJ-230-D	XF-1607-FAR
J	1/0.315mm	100m	WJ-230-D	XF-1608-FAR
K	1/0.508mm	25m	WK-352-D	XF-1253-FAR
K	1/0.508mm	50m	WK-352-D	XF-1258-FAR
K	1/0.508mm	100m	WK-352-D	XF-1799-FAR
K	7/0.2mm	10m	WK-353-D	XF-1663-FAR
K	7/0.2mm	25m	WK-353-D	XF-1662-FAR
K	7/0.2mm	50m	WK-353-D	XF-1664-FAR
K	7/0.2mm	100m	WK-353-D	XF-1665-FAR
K	1/0.2mm	10m	WK-363-D	XF-1669-FAR
K	1/0.2mm	25m	WK-363-D	XF-1668-FAR
K	1/0.2mm	50m	WK-363-D	XF-1670-FAR
K	1/0.2mm	100m	WK-363-D	XF-1671-FAR
N	1/0.315mm	10m	WN-130-D	XF-1680-FAR
N	1/0.315mm	25m	WN-130-D	XF-1679-FAR
N	1/0.315mm	50m	WN-130-D	XF-1681-FAR
N	1/0.315mm	100m	WN-130-D	XF-1682-FAR