

Datasheet

# ANSI PVC Insulated Thermocouple Cable with Miniature Thermocouple Plug & Socket

ANSI Colour Coded



## Cable Description

- PVC insulated flat pair construction
- Conductors laid flat PVC insulated with overall PVC sheath
- All round general purpose cable, both waterproof and very flexible
- Thermocouple extension types K, 5 Metre lengths available
- Conductors 7/0.2mm
- Tolerance Class 2
- Insulation rating -10°C to 105°C
- Colour code (cores & jacket) in accordance with ANSI specification

## Connector Description

- Ideal for general purpose use
- All contacts are polarised to ensure correct connection
- Colour coded in accordance with ANSI specification
- Maximum continuous operating temperature 220°C

Type	Length	Connector Size	Description	Order Number
K	5 metre	Miniature	EXT-K-C1-5.0-MP-MS	<b>XF-1853-FAR</b>