

# GluePRO 300

Case  
EAN 4007841 052683  
Article number 052683



&lt;3 min.

Quickstart



190 °C

ø 11 mm

Glue sticks



CE



EMC

## Function description

The new benchmark. The rugged GluePRO 300 with non-slip grip handle is comfortable to hold and has what it takes to become one of your favourite tools. This hot melt glue applicator is the key to convenient, reliable and tireless gluing work without compromising on anything. Practical stroke adjustment makes it possible to set the quantity of glue per stroke for any specific application. Warm-up time is approximately three minutes. Temperature: 190°C. Includes practical case.

## Technical specifications

Output	300 W	Heating element	Tubular heating element
Temperature	190 °C	Voltage range (min)	220 V
Warm-up time	3 min	Restart protection	Yes
Delivery rate	25 gr/min	Melt temperature	190 °C
Max. stick diameter	11.7 mm	Cord length	max.
Function, hanger	Yes	Dimensions (L x W x H)	230 x 70 x 290 mm
Soft grip	Yes	Version	Case
Idle mode	No	PU1, net weight	0,58 kg
Nozzle can be changed	Yes	Manufacturer's Warranty	1 year
Stroke adjustment	Yes	PU1, EAN	4007841052683
Temperature, adjustable	No	Netzstecker	Typ F
Temperature accuracy +/-	3 °C		

## Accessories

EAN 4007841 052737

Long nozzle

EAN 4007841 052744

Long nozzle, angled, ø 3.0 mm

Hot-melt glue applicator - Professional Line

# GluePRO 300

Case  
EAN 4007841 052683  
Article number 052683



## Accessories

EAN 4007841 052928	Long nozzle, Ø 1.5 mm
EAN 4007841 052935	Long nozzle
EAN 4007841 052423	Flex glue sticks Ø 11 mm
EAN 4007841 052430	Fast glue sticks Ø 11 mm
EAN 4007841 050092	General-purpose glue sticks Ø 11 mm