

Cordless hot air tool - Professional Line

# mobile heat MH3

UK including rechargeable 5.5Ah battery and charger  
EAN 4007841 068332  
Article number 068332



CE

## Function description

Mobile. Fast. Precise. mobile heat MH3, the 18 V cordless hot air tool with 2 temperature settings (300°C/500°C). Heats up to 300°C in a maximum of 5 seconds. High-performance, with an airflow rate of up to 200 l/min. The security lock button and LED illumination on the base of the tool ensure safe working. Compatible with all push-on standard nozzles from STEINEL. Including case (upon request, with CAS rechargeable battery and charger)

## Technical specifications

Temperature	300 – 500 °C	Function, hanger	Yes
Airflow rate	200 l/min	Function, life expectancy, motor	500 h
Temperature setting	2-stage	Function, life expectancy, heating element	300 h
Settings made via	multiple-stage switch	Replaceable heating element	No
Temperature display	LED segment display	Restart protection	No
Airflow control	Settings	Temperature scanner	No
Programming function	No	Power supply, detail	Rechargeable lithium-ion battery
Loc function	No	Fine dust filter	No
Residual heat indicator	No	Thermal cut-out	Yes
Cool function	No	Thermostat	No
Motor, type	Brush motor	ESD	No
Heating element	Ceramic heating element	Nozzle receiver, type	34
Mains power supply	18 V	Dimensions (L x W x H)	225 x 72 x 204 mm
Rechargeable battery voltage	18 V	PU1, net weight	0,68 kg
Rechargeable battery capacity	5.5	Manufacturer's Warranty	1 year
Interface	Metabo rechargeable battery	PU1, EAN	4007841068332

<https://www.steinell.de>

Subject to technical modifications

10.2022 Page 1 from 2

Cordless hot air tool - Professional Line

# mobile heat MH3

UK including rechargeable 5.5Ah battery and charger  
EAN 4007841 068332  
Article number 068332



## Accessories

EAN 4007841 068257

Spare CAS battery 18V LiHD

---