

mobile heat MH5

including rechargeable 5.5Ah battery and charger
 EAN 4007841 068233
 Article number 068233



CE

Function description

Mobil. Fast. Powerful. Mobile heat MH5, the 18 V cordless hot air tool with flexible setting options. Temperatures from 50°C to 500°C, with 6 airflow rates (up to 300 l/min) for any application. Ready for use in less than 4 seconds. LCD display for a perfect overview and settings. 4 preset application-specific programmes – can be changed at any time. The security lock button and LED illumination on the base of the tool ensure safe working. Compatible with all push-on standard nozzles from STEINEL. Including case, 5.5 Ah CAS rechargeable battery and charger.

Technical specifications

Temperature	50 – 500 °C
Airflow rate	300 l/min
Temperature setting	in 10°C steps by joystick
Settings made via	joystick
Temperature display	LCD display
Airflow control	Settings
Programming function	Yes
Loc function	No
Residual heat indicator	No
Cool function	No
Motor, type	Brush motor
Heating element	Ceramic heating element
Mains power supply	18 V
Rechargeable battery voltage	18 V
Rechargeable battery capacity	5.5
Interface	Metabo rechargeable battery

Function, hanger	Yes
Function, life expectancy, motor	500 h
Function, life expectancy, heating element	300 h
Replaceable heating element	No
Restart protection	No
Temperature scanner	No
Power supply, detail	Rechargeable lithium-ion battery
Fine dust filter	No
Thermal cut-out	Yes
Thermostat	No
ESD	No
Nozzle receiver, type	34
Dimensions (L x W x H)	225 x 72 x 204 mm
PU1, net weight	2,253 kg
Manufacturer's Warranty	1 year
PU1, EAN	4007841068233

Cordless hot air tool - Professional Line

mobile heat MH5

including rechargeable 5.5Ah battery and charger

EAN 4007841 068233

Article number 068233



Accessories

EAN 4007841 068257	Spare CAS battery 18V LiHD
EAN 4007841 068240	Spare CAS battery 18V LiHD
EAN 4007841 068349	CAS Fast Charger ASC 145
EAN 4007841 068035	Adapter nozzle
EAN 4007841 075569	12-piece hot-air accessory kit
EAN 4007841 075811	Shrink tubing kit
EAN 4007841 058821	Pro Cut cutting system
EAN 4007841 006785	Pressure roller 40mm - Silicone