

Hot air tool

# HL 2020 E

Folding box  
EAN 4007841 008192  
Article number 008192



CE



VDE

## Function description

The master class. Electronically controlled hot air tool HL 2020 E with LCD. Professional technology for shaping tiles, de-soldering circuit boards, welding plastics, drying repair filler, shrinking cable sleeves, soldering pipes and a whole lot more. Adjustable by joystick from 80°C to 630°C in 10°C steps. Residual heat indicator to prevent burns.

## Technical specifications

|                                  |                           |
|----------------------------------|---------------------------|
| Temperature                      | 80 – 630 °C               |
| Airflow rate                     | 150 – 500 l/min           |
| Temperature setting              | in 10°C steps by joystick |
| Settings made via                | joystick                  |
| Temperature display              | LCD display               |
| Airflow control                  | Continuous                |
| Programming function             | No                        |
| Loc function                     | No                        |
| Residual heat indicator          | Yes                       |
| Cool function                    | No                        |
| Motor, type                      | Brush motor               |
| Heating element                  | Ceramic heating element   |
| Mains power supply               | 220 – 230 V / 50 – 60 Hz  |
| Function, hanger                 | Yes                       |
| Function, life expectancy, motor | 600 h                     |

|  |                   |
|--|-------------------|
| Function, life expectancy, heating element | 600 h             |
| Replaceable heating element                | No                |
| Restart protection                         | No                |
| Temperature scanner                        | Yes               |
| Fine dust filter                           | No                |
| Thermal cut-out                            | Yes               |
| Thermostat                                 | Yes               |
| ESD  | No                |
| Nozzle receiver, type                      | 34                |
| Cord length                                | 2.2 m             |
| Dimensions (L x W x H)                     | 253 x 86 x 200 mm |
| PU1, net weight                            | 0,88 kg           |
| Manufacturer's Warranty                    | 3 years           |
| PU1, EAN                                   | 4007841008192     |

Hot air tool

# HL 2020 E

Folding box  
EAN 4007841 008192  
Article number 008192



## Accessories

|                    |  |
|--------------------|--|
| EAN 4007841 014919 | Temperature scanner HL Scan            |
| EAN 4007841 078218 | Fine dust filter HL 1920 E - HG 2320 E |
| EAN 4007841 009625 | HL Light                               |
| EAN 4007841 010317 | Paint Scraper Set                      |
| EAN 4007841 074210 | ABS plastic welding rod                |
| EAN 4007841 073411 | PP plastic welding rod                 |
| EAN 4007841 071219 | HDPE plastic welding rod               |
| EAN 4007841 073114 | PVC plastic welding rod                |
| EAN 4007841 006648 | Crimp connectors - Ø 1.5 - 2.5 mm      |
| EAN 4007841 072766 | Shrink tubing III - Ø 4,8 - 12,0 mm    |
| EAN 4007841 006662 | Crimp connectors - Ø 0.1 - 6.0 mm      |
| EAN 4007841 071318 | Shrink tubing I - Ø 1,6 - 4,8 mm       |
| EAN 4007841 006655 | Crimp connectors - Ø 0.5 - 1.5 mm      |
| EAN 4007841 070717 | Reduction nozzle 14 mm                 |
| EAN 4007841 074715 | Wide-slit nozzle                       |
| EAN 4007841 012311 | Feed roller                            |
| EAN 4007841 071417 | Shrink tubing II - Ø 4,8 - 9,5 mm      |
| EAN 4007841 070212 | Surface nozzle 75 mm                   |
| EAN 4007841 075811 | Shrink tubing kit                      |
| EAN 4007841 070915 | Welding nozzle                         |
| EAN 4007841 070113 | Surface nozzle 50 mm                   |
| EAN 4007841 070311 | Window nozzle 50 mm                    |
| EAN 4007841 070519 | Reflector nozzle                       |
| EAN 4007841 070410 | Window nozzle 75 mm                    |
| EAN 4007841 074616 | Soldering reflector nozzle 10 mm       |
| EAN 4007841 034566 | HL Tool Stand                          |
| EAN 4007841 070618 | Reduction nozzle 9 mm                  |