

acer



PROJECT WITH CLARITY



Acer X1226AH

4,000 ANSI lumens

20,000:1 contrast ratio

Acer LumiSense content-aware

Acer Bluelight Shield



BluelightShield™



LUMISENSE



ColorSafe™ II



ColorBoost 3D

Feature Highlights

Expressive display

- XGA (1,024 x 768) resolution
- 4,000 ANSI lumens
- 20,000:1 Dynamic Black
- Acer LumiSense
- Acer Bluelight Shield
- Acer ColorBoost3D
- Acer ColorSafe II
- HDMI 3D

Enhanced usability

- Wireless Projection^{1, 2}
- 3W built-in speaker
- AC power on

Installation flexibility

- Auto keystone +/- 40 degree
- Auto ceiling-mounted correction

Eco-friendly functionality

- Acer EcoProjection
- Lamp life up to 10,000 hours (ExtremeEco mode)

1 – Optional wireless dongle is required for wireless projection.
 2 – Additional device must support Miracast technology.

Model name	X1226AH
Projection system	DLP®
Resolution	XGA (1,024 x 768) Maximum WUXGA (1,920 x 1,200)
Brightness	4,000 ANSI Lumens (Standard), 3,200 ANSI Lumens (ECO) (Compliant with ISO 21118 standard)
Aspect ratio	4:3 (Native), 16:9 (Supported)
Contrast ratio	20,000:1
Throw ratio	1.94 ~ 2.16 (51"@2m)
Zoom ratio	1.1X
Projection lens	F= 2.41~2.53, f = 21.85~24.01mm Manual Zoom & Focus
Lamp life	6,000 Hours (Standard), 7,000 Hours (ECO), 10,000 Hours (ExtremeEco)
Noise level	32 dBA (Standard), 24 dBA (ECO)
Input interface	Analog RGB/Component Video (D-sub) x 1 HDMI (Video, Audio, HDCP) x 1 PC Audio (Stereo mini jack) x 1 Composite Video (RCA) x 1
Output interface	PC Audio (Stereo mini jack) x 1 DC Out (5V/1A, USB Type A) x 1 Analog RGB (D-sub) x 1
Control interface	RS232 (D-sub) x 1 USB (Type A) x 1, share output port
Dimensions	313 x 240 x 113.7mm (12.3" x 9.4" x 4.5")
Weight	2.8 Kg (6.17 lbs)

Product View

