

acer



PROJECTING THE FUTURE BUSINESS

Acer P1557Ki

- 4,500 lumens brightness
- Acer Bluelight Shield
- Acer LumiSense
- 10,000:1 Dynamic Black
- Wireless hidden dongle display



Wireless Projection



Brightness



BluelightShield™



LUMISENSE



ColorSafe II



ColorBoost 3D

Feature Highlights

Expressive display

- 1080p (1,920 x 1,080)
- 4,500 ANSI lumens
- Dynamic Black 10,000:1
- Acer BlueLight Shield
- Acer LumiSense
- Acer ColorBoost3D
- Acer ColorSafe II
- HDMI 3D

Enhanced usability

- Wireless projection frees you from cable chaos (Default)
- 10W built-in speaker
- AC power on


Installation flexibility

- +/-40° (Vertical, Manual & Auto) Keystone
- Auto ceiling-mounted correction

Eco-friendly functionality

- Acer EcoProjection
- Up to 20,000 hours lamp life (EcoPro)

Model name	P1557Ki
Projection system	DLP™
Resolution	Native 1080p (1,920 x 1,080) Maximum WUXGA (1,920 x 1,200)
Brightness	4,500 ANSI Lumens (Standard), 3,600 ANSI Lumens (ECO), (Compliant with ISO 21118 standard) * 4500lm Brightness is under WUXGA resolution
Aspect ratio	16:9 (Native), 4:3 (Supported)
Contrast ratio	Dynamic Black 10,000:1
Throw ratio	1.125~1.46 (80" @2m)
Projection lens	F = 1.94 ~ 2.07, f = 11.9 mm ~ 15.5 mm, Manual Zoom and Manual Focus
Keystone correction	+/-40° (Vertical, Manual & Auto)
Lamp life	4,000 Hours (Standard), 10,000 Hours (ECO), 20,000 Hours (EcoPro)
Noise level	29 dBA (ECO)
Input interface	HDMI 1.4a (Video, Audio, HDCP 1.4) x 2 PC Audio (Stereo mini jack) x 1 USB (Wireless dongle, Type A) x 1
Output interface	PC Audio (Stereo mini jack) x 1 DC Out (5V/1.5A, USB Type A) x 1
Control	RS232 (D-sub) x 1
Dimensions	322 x 225 x 91 mm (12.7" x 8.9" x 3.6")
Weight	2.9 Kg (6.4 lbs)



Standard Accessory



Wireless

Optional Accessory

