

acer



**BRIGHT,
CLEAR**



Acer X1328WKi

4,500 lumens brightness
WXGA and WUXGA Resolution
Acer Bluelight Shield
Acer LumiSense
20,000:1 Dynamic Black



Wireless Projection



Brightness



Dynamic black



BluelightShield™



LUMISENSE



ColorSafe II



ColorBoost 3D



ExtremeEco

Expressive display

- WXGA Resolution
- 4,500 ANSI lumens
- Dynamic Black 20,000:1
- Acer Bluelight Shield
- Acer LumiSense
- Acer ColorBoost3D
- Acer ColorSafe II
- HDMI 3D with 144Hz 24p

Enhanced usability

- Wireless projection
- Hidden dongle design
- 3W built-in speaker
- 24/7 operation

Installation flexibility


- 40-degree auto keystone correction
- Auto ceiling-mounted correction
- AC power on
- I/O power on

Eco-friendly functionality

- Acer EcoProjection
- Lamp life up to 15,000 hours in ExtremeEco mode

Model name	X1328WKi
Projection system	DLP™
Resolution	Native WXGA (1,280 x 800) Maximum WUXGA (1,920 x 1,200)
Brightness	4,500 ANSI Lumens (Standard), 3,600 ANSI Lumens (ECO) (Compliant with ISO 21118 standard)
Aspect ratio	16:10 (Native), 4:3/16:9 (Supported)
Contrast ratio	Dynamic Black 20,000:1
Throw ratio	1.54 ~ 1.72 (60"@2m)
Projection lens	F= 2.41~2.53, f = 21.85~24.00mm Manual Zoom & Focus
Keystone correction	+/-40° (Vertical, Manual & Auto)
Lamp life	6,000 Hours (Standard), 10,000 Hours (ECO), 15,000 Hours (ExtremeEco)
Noise level	27 dBA (ECO)
Input interface	HDMI1.4a (Video, Audio, HDCP) x 1 PC Audio (Stereo mini jack) x 1 USB (Wireless dongle, Hidden Type A2.0) x 1
Output interface	DC Out (5V/1A, USB Type A) x 1 PC Audio (Stereo mini jack) x 1
Control	RS232 (D-sub) x 1
Dimensions	313 x 240 x 113.7mm (12.3" x 9.4" x 4.5")
Weight	2.75kg (6.06lb)

Product Views



Standard Accessory

Optional Accessory