

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1202470001](#)  
**Status:** **Active**  
**Overview:** Brad Passive-Signal and Safety MPIS Boxes  
**Description:** MPIS Nano-Change (M8) Passive Junction Box, Top-Mount, 4 Ports, LED for PNP Sensor, WSOR Cable, 5.0m Length  
**Replacement Part Number :** <http://www.molex.com/molex/search/partSearch?pQuery=&sType=p&query=12011300061201130006>

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)



*Series image - Reference only*

**Agency Certification**

UL E152210

**General**

Product Family Passive Distribution Boxes  
 Series [120247](#)  
 IP Rating IP67, IP68  
 Overview [Brad Passive-Signal and Safety MPIS Boxes](#)  
 Product Name MPIS  
 Replacement Part Number [1201130006](#)  
 Taxonomy Passive Distribution Boxes  
 UPC 889056129466

**Physical**

Bus I/O N/A  
 Cable Connector Orientation Straight  
 Cable Length 5.0m  
 Home Run Cable Length 5.0m  
 Home Run Connector N/A  
 Home Run Interface Pigtail  
 Keyway A-coded  
 LED Indicator PNP Sensors  
 Material - Cable Jacket TPU  
 Material - Housing PBT  
 Material - Metal Copper Alloy  
 Material - Plating Mating Gold  
 Net Weight 469.800/g  
 Orientation Top-Mount  
 Poles 3  
 Poles (wired) 3  
 Ports 4  
 Temperature Range - Operating -25°C to +85°C  
 Wire/Cable Type WSOR  
 Wiring Configuration Single I/O per Port

**Electrical**

Current - Maximum per Contact 2.0A per port, 6.0A per module  
 Functional Wiring PNP  
 Voltage - Maximum 10-30V DC

**Material Info**

Engineering Number BEB401P-FBW-05

**Reference - Drawing Numbers**

Sales Drawing 1202470001-000

**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Contained

**Search Parts in this Series**

[120247 Series](#)

This document was generated on 10/03/2022

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**