

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200908037](#)
Status: **Active**
Overview: [Brad Nano-Change \(M8\) Products](#)
Description: Nano-Change (M8) Receptacle, M8 x 1.0 Mounting Threads, Female (Straight) to Leads, 4 Poles, 0.20m (7.87") Length, Back Panel Mount

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Industrial Receptacles
Series	120090
IP Rating	IP67
NEMA Rating	NEMA 6
Overview	Brad Nano-Change (M8) Products
Product Name	Nano-Change (M8)
Taxonomy	Circular Industrial Connectors
Type	Single Ended (pigtail)
UPC	887191151762

Physical

Coupling Type	Internal Thread
Gender	Female
Keyway	A-coded
Length	0.20m
Material - Component	Nickel-plated Brass
Mounting Thread Size	M8 x 1.0
Net Weight	12.000/g
Orientation	Straight
Panel Mount	Back
Poles	4
Temperature Range - Operating	-25° to +85°C
Wire Size AWG	24
Wire/Cable Type	UL 1569

Electrical


Current - Maximum per Contact	3.0A
Voltage - Maximum	30V AC/DC

Material Info

Engineering Number	4R4L40E02C200
--------------------	---------------

Reference - Drawing Numbers

Sales Drawing	1200905104-000
---------------	----------------



EU ELV

Not Reviewed

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per - D(2022)4187-DC (10 June 2022)

Lead

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

ZZCERT_CE -

Declaration of

Conformity

ZZCERT_UKCA

- Declaration of

Conformity

China RoHS

Not Relevant

Not Reviewed

Not Contained

CER_4000410038_00_000.pdf

CER_4000410299_00_000.pdf

Search Parts in this Series

[120090 Series](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION