

MW2P045 - 45W UK-US Plugtop Voltage Converter

[Home](#) > [Products](#) > [Voltage Converters](#) > 45W UK-US Plugtop Voltage Converter

Features

- Fully enclosed ABS housing
- Compact size
- Allows the use of USA appliances in the UK
- Thermal fuse protection

Standards



Description

NB: This product is not suitable for appliances requiring an earth or more than 45W rated power.



Specification

Input Voltage	230AC \pm 10%
Input Frequency	50Hz
Output Voltage	110V AC
Maximum Output Power	45W
Protector	IP 20
Operating Temperature	-10°C to +25°C
Storage Temperature	-25°C to +70°C

Items

Part Code

Part Code	Dimensions
MW2P045	88 x 62 x 88mm