

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2192640001](#)
Status: **Active**
Overview: Combo Antennas
Description: Sunshade 5-in-1 (5G/Wi-Fi/GPS) Antenna Lite, 95.00mm x 95.00mm, 1000.00mm Cables with SMA Plug Male Connectors, Adhesive Mounting

Documents:

3D Model	Application Specification 2192640001-000 (PDF)
Drawing (PDF)	Packaging Specification 2192640001-001 (PDF)
3D Model (PDF)	Datasheet (PDF)
Product Specification 2192640001-001 (PDF)	RoHS Certificate of Compliance (PDF)



General

Product Family	Antennas
Series	219264
Component Type	External Antenna
Function	Signal
Overview	Combo Antennas
Product Name	Sunshade 5-in-1 Antenna Lite
Protocol	Cellular, GPS, Wi-Fi
Taxonomy	Antennas
Type	External Antenna
UPC	196823076343

Physical

Cable Length	1000.00mm
Length	95.00mm
Mounting Style	Adhesive
Net Weight	267.020/g
Packaging Type	PET Bag
Polarization	Linear, RHCP
Radiation Pattern	High Directivity (GPS), Omnidirectional (4G,WiFi)
Thickness	38.00mm
Width	95.00mm

Electrical

Band#1 F_End (MHz)	1602
Band#1 F_Start (MHz)	1561
Band#2 F_End (MHz)	960
Band#2 F_Start (MHz)	698
Band#3 F_End (MHz)	2690
Band#3 F_Start (MHz)	1710
Band#4 F_End (MHz)	4200
Band#4 F_Start (MHz)	3300
Band#5 F_End (MHz)	5000
Band#5 F_Start (MHz)	4400
Band#6 F_End (MHz)	2500
Band#6 F_Start (MHz)	2400
Band#7 F_End (MHz)	5850
Band#7 F_Start (MHz)	5150
Band#8 F_End (MHz)	7125
Band#8 F_Start (MHz)	5925
Electrical Connectivity	Cable, SMA Plug Male Connector
Peak Gain (dBi)	See Product Specification
Return Loss - S11 (dB)	< -10, < -4, < -5, < -8
Total Efficiency	See Product Specification

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 7(c)-I,6(c)

REACH SVHC

Contained Per -
D(2022)4187-DC (10
June 2022)

Lead

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[219264](#) Series

Mates With

SMA Jack Female Receptacle

Material Info

Reference - Drawing Numbers

Application Specification	2192640001-000
Packaging Specification	2192640001-001
Product Specification	2192640001-001
Sales Drawing	2192640001-000

This document was generated on 12/09/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION