


# ROLINE HDMI Splitter, 4K, 2-way

<b>Product No.</b>	14.01.3585
<b>Manufacturer</b>	ROLINE
<b>Manufacturer No.</b>	14.01.3585
<b>EAN (single piece)</b>	7611990145911

**roline**  
Designed for Professionals



**2160p**  
UHD-1

**4K**

**3D**  
capable

**Reproduces an HDMI video signal, e.g. From a BluRay/DVD player, to 2 output devices with a maximum resolution of 3840x2160 @60Hz!**

- Duplicates a HDMI video signal to two HDMI video signals with a 4K resolution
- Connectors: 1 HDMI Input (for e.g. BluRay/DVD-player), 2 HDMI outputs
- Supports 480i, 480p, 720i, 720p, 1080i, 1080p, 2160p @60Hz
- Supports VGA, SVGA, XGA, UXGA
- Supports 3D
- Plug & play, easy to install and simple to operate
- No software installation required
- Power supply included (5VDC, 2A)

**ROLINE 2-Port HDMI splitter for image transfers up to 4K2K Ultra HD and in 3D quality**

The ROLINE HDMI video splitter allows you to distribute picture and sound signals reliably to up to two HDMI indicators without any loss of quality. For example, video formats from PC or notebook can be distributed to two devices such as a monitor, TV or projector. An additional power supply is included in the delivery. The high-quality metal housing improves the shielding of the signals and provides an absolutely interference-free data transfer. The ROLINE HDMI Splitter is particularly suitable for professional use, e.g. For training purposes or in advertising, which is to be carried out in high resolution with up to 4k. No software is

required.

### Technical specifications

Manufacturer	ROLINE
Product group	Splitters and selectors
Product type	HDMI-Video-Splitter
Colour	black
Scope of delivery	splitter, manual, powersupply
Interface	HDMI
Inputs	1
Outputs	2
Video input	1x HDMI Female
Video output	2x HDMI Female
Max. resolution (nom.)	3840 x 2160 @60Hz
Dimensions (HxWxD)	20 x 80 x 51 mm
Power supply output	5 VDC; 2A
Height	20 mm
Width	80 mm
Depth	51 mm
Weight	168.1 g
Height of packaging (single piece)	60 mm
Width of packaging (single piece)	130 mm
Depth of packaging (single piece)	170 mm
Package weight (single piece)	0.3 kg