

NYS355

Phono jack to jack adapter



Article Variations

Article Name	Details	Packaging
NYS355		

Technical Information

Product

Title	NYS355
Connection Type	Jack

Electrical

Contact Resistance	≤10 mΩ
Insulation Resistance	>2000 MΩ(Initial)
Rated Voltage	0.5 VAC

Mechanical

Insertion and Withdrawal Force	5-20N
Lifetime	>5000 Mating Cycles

Material

Housing	Brass
Jack	Brozen
Wire	Brass
Insulating tube	PVC
Bushing	PC
Washer	ABS
Housing	Nickel plating
Jack	Snce6 plating