

# Short tape measures



## Heavy-duty hook

**TENSILE STRENGTH EXCEEDS 1,000 N (100 KG)**




Non-slip serrations.



With stainless steel reinforcing plate.



Multi rivets.



Wide hook with protective lugs. Multi-functional.

## ▶ ABS Case Series



## Series 893

### COMPACT AND TOUGH



#### Easily accessible tape lock

For keeping a measurement, making comparative measurements, marking-out, etc.



#### Stainless steel belt clip

• For easy carrying.



#### Wrist strap hole

• Avoids dropping the tape, frees the hand. Hole (except 893.316F)

#### Functional case

• Base and bearing face at 90°. Rounded additional length.




## ABS case tape measure - 2 metres with lock

### 893.213

- 2 m x 13 mm matt, anti-glare, nylon-coated blade.
- Blade rigidity : 1.30 m vertically - 1.20 m horizontally.
- 2-rivet hook with stainless steel reinforcing plate.
- Internal measurement obtained by adding dimension A (see table).
- Ergonomic ABS case.
- Blister card presentation (145x96 mm).

	↔	↕	A	C x D	ΔΔ
	m	mm	mm	mm	g
<b>893.213</b>	2	13	55	53 x 24	78



## ABS case tape measure - 3 metres with lock

### 893.316

- 3 m x 16 mm matt, anti-glare, nylon-coated blade.
- Blade rigidity : 1.80 m vertically - 1.50 m horizontally.
- 2-rivet hook with stainless steel reinforcing plate.
- Internal measurement obtained by adding dimension A (see table).
- Ergonomic ABS case.
- Blister card presentation (145x96 mm).

	↔	↕	A	C x D	ΔΔ
	m	mm	mm	mm	g
<b>893.316</b>	3	16	60	60 x 27	126

