



## Main

Product or Component Type	Lug shield
Poles description	3P
Quantity per Set	Set of 6

## Complementary

Height	1.57 in (40 mm)
Width	1.18 in (30 mm)
Depth	1.38 in (35 mm)
Net Weight	0.12 lb(US) (0.055 kg)
IP degree of protection	IP20 conforming to IEC 60529
Range Compatibility	TeSys G
Product Compatibility	LC1G115...225 LC1G265...500 LC1G630...800

## Environment

Pollution degree	3 IEC 60947-1
Standards	EN/IEC 60947-4-1 UL 60947-4-1 CSA C22.2 No 60947-4-1 GB/T 14048.4
Operating altitude	9842.52 ft (3000 m) without derating 5000 m with derating factor
Ambient Air Temperature for Storage	-76...176 °F (-60...80 °C)
Ambient Air Temperature for Operation	-13...140 °F (-25...60 °C)

## Ordering and shipping details

Category	22328-TESYS GIGA ACCESSORIES
Discount Schedule	I12
GTIN	3606481047847
Returnability	No

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.59 in (1.5 cm)
Package 1 Width	3.74 in (9.5 cm)
Package 1 Length	5.51 in (14.0 cm)
Package 1 Weight	0.95 oz (27.0 g)
Unit Type of Package 2	S02

Number of Units in Package 2	50
Package 2 Height	5.91 in (15.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	3.74 lb(US) (1.697 kg)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Styrene, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
PVC free	Yes
Halogen content performance	Halogen free plastic parts product