


DG 30 Socket

UD profile

Socket, hand-operated, chrome-vanadium steel 31CrV3, chrome-plated, not standardised.

Code	No.	Ø mm	L	d ₁	d ₂	t	↺↻
6240630	DG 30 10	10	45,0	14,7	17,3	9,0	55
6240710	DG 30 11	11	45,0	16,0	17,3	9,0	55
6240980	DG 30 12	12	45,0	17,2	17,3	9,0	60
6241520	DG 30 13	13	45,0	18,5	17,3	9,0	60
6241600	DG 30 14	14	47,0	19,7	17,3	12,0	60
6241790	DG 30 15	15	49,0	21,0	17,3	12,5	65
6241870	DG 30 16	16	49,0	22,2	17,3	12,5	70
6241950	DG 30 17	17	49,5	23,5	17,3	12,5	70
6242410	DG 30 18	18	49,5	24,7	17,3	12,5	75
6242680	DG 30 19	19	49,5	26,0	17,3	12,5	75




TX 30 Socket

for protruding TORX® head screws

Socket, hand-operated, with square drive as per DIN 3120 - C 10, ISO 1174 with ball retaining groove, knurled grip. In GEDORE vanadium steel 31CrV3, mat. No. 1.2208, chrome-plated, polished.

© = reg. trademark of Camcar-Textron Inc. USA

Code	No.	□ M	mm	L	d ₁	d ₂	↺↻
6250270	TX 30 E5	M 4	4,75	28	7,2	17,5	25
6250350	TX 30 E6	M 5	5,74	28	8,5	17,5	25
6250430	TX 30 E7	M 6	6,22	28	9,5	17,5	25
6250510	TX 30 E8	M 6 - M 7	7,52	28	10,8	17,5	25
6250780	TX 30 E10	M 8	9,42	28	13,2	17,5	30
6250860	TX 30 E11	-	10,08	28	13,8	17,5	30
6250940	TX 30 E12	M 10	11,17	28	15,2	17,5	30
6251080	TX 30 E14	M 12	12,90	28	16,8	18,3	35



ITX 30 Screwdriver bit socket


for recessed TORX® head screws

Screwdriver bit socket, hand-operated, pressed-in hexagon pin. With square drive as per DIN 3120 - C 10, ISO 1174 with ball retaining groove, knurled grip.

Chrome-plated, bit in GEDORE vanadium special steel, gun-metal finish.

© = reg. trademark of Camcar-Textron Inc. USA

Code	No.	□ M	mm	L	t	↺↻
6246320	ITX 30 T20	M 4 - M 5	3,86	49	17	45
6246830	ITX 30 T25	M 4,5 - M 5	4,43	49	17	45
6247210	ITX 30 T27	M 4,5 - M 6	4,99	49	17	45
6247560	ITX 30 T30	M 6 - M 7	5,52	49	17	45
6247720	ITX 30 T40	M 7 - M 8	6,65	49	17	45
6247800	ITX 30 T45	M 8 - M 10	7,82	49	17	50
6247990	ITX 30 T50	M 10	8,83	49	17	70



ITX 30 L Screwdriver bit socket

long, for recessed TORX® head screws

Screwdriver bit socket, hand-operated, pressed-in hexagon pin. With square drive as per DIN 3120 - C 10, ISO 1174 with ball retaining groove, knurled grip.

Chrome-plated, bit in GEDORE vanadium special steel, gun-metal finish.

© = reg. trademark of Camcar-Textron Inc. USA

Code	No.	□ M	mm	L	t	↺↻
1394177	ITX 30 L T20	M 4 - M 5	3,86	94	62	45
1394185	ITX 30 L T25	M 4,5 - M 5	4,43	94	62	45
1394193	ITX 30 L T27	M 4,5 - M 6	4,99	94	62	45
1394207	ITX 30 L T30	M 6 - M 7	5,52	94	62	45
1394215	ITX 30 L T40	M 7 - M 8	6,62	94	62	45
1394223	ITX 30 L T45	M 8 - M 10	7,82	94	62	50
1394231	ITX 30 L T50	M 10	8,83	94	62	70

