

INX 19 Screwdriver bit socket

for multi-point screws

Screwdriver bit socket, hand-operated, pressed-in hexagon pin. With square drive as per DIN 3120 - C 12.5, ISO 1174 with ball retaining groove, knurled grip. Chrome-plated, bit in GEDORE vanadium special steel, gun-metal finish. * not standardised

Code	No.		L mm		
6158890	INX 19 5*	M 5	55	17	60
6159000	INX 19 6*	M 6	55	17	65
6159270	INX 19 8	M 8	55	17	70
6159430	INX 19 10	M 10	55	17	75
6159780	INX 19 12	M 12	55	17	80



INX 19 L Screwdriver bit socket

long, for multi-point screws

Description as INX 19.

* not standardised

Code	No.		L mm		
6159190	INX 19 L 6-100*	M 6	100	62	80
6159350	INX 19 L 8-100	M 8	100	62	100
6159510	INX 19 L 10-100	M 10	100	62	105
6159860	INX 19 L 12-100	M 12	100	62	105



ITX 19 Screwdriver bit socket

for recessed TORX® head screws

Screwdriver bit socket, hand-operated, pressed-in hexagon pin. With square drive as per DIN 3120 - C 12.5, ISO 1174 with ball retaining groove, knurled grip. Chrome-plated, bit in GEDORE vanadium special steel, gun-metal finish.

© = reg. trademark of Camcar-Textron Inc. USA

Code	No.		★ mm	L	t	
6152930	ITX 19 T20	M 4 - M 5	3,86	55	17	60
6154200	ITX 19 T25	M 4,5 - M 5	4,43	55	17	65
6154630	ITX 19 T27	M 4,5 - M 6	4,99	55	17	65
6156170	ITX 19 T30	M 6 - M 7	5,52	55	17	65
6156330	ITX 19 T40	M 7 - M 8	6,65	55	17	65
6157060	ITX 19 T45	M 8 - M 10	7,82	55	17	70
6158030	ITX 19 T50	M 10	8,83	55	17	90
6158380	ITX 19 T55	M 12	11,22	55	17	110
6158540	ITX 19 T60	M 14	13,25	55	15	110




ITX 19 L Screwdriver bit socket

long, for recessed TORX® head screws

Description as ITX 19.

© = reg. trademark of Camcar-Textron Inc. USA

Code	No.		★ mm	L	t	
6188020	ITX 19 L T20-100	M 4 - M 5	3,86	100	62	80
6188100	ITX 19 L T25-100	M 4,5 - M 5	4,43	100	62	85
6188370	ITX 19 L T27-100	M 4,5 - M 6	4,99	100	62	85
6152500	ITX 19 L T30-100	M 6 - M 7	5,52	100	62	85
6152690	ITX 19 L T40-100	M 7 - M 8	6,65	100	62	85
6155870	ITX 19 L T45-100	M 8 - M 10	7,82	100	62	90
6158700	ITX 19 L T50-100	M 10	8,83	100	62	105
6159940	ITX 19 L T55-100	M 12	11,22	100	62	155
6188450	ITX 19 L T60-100	M 14	13,25	100	60	155
6105180	ITX 19 L T70-100	M 16	15,55	100	60	170



ITX 19 B Screwdriver bit socket

for recessed TORX® head screws with pilot

Description as ITX 19.

© = reg. trademark of Camcar-Textron Inc. USA

Code	No.		★ mm	L	t	Bore	
6192720	ITX 19 B T20	M 4 - M 5	3,86	55	17	1,55 x 1,86	60
6195660	ITX 19 B T25	M 4,5 - M 5	4,43	55	17	1,93 x 2,04	65
6196390	ITX 19 B T27	M 4,5 - M 6	4,99	55	17	2,18 x 2,29	65
6200170	ITX 19 B T30	M 6 - M 7	5,52	55	17	2,56 x 2,92	65
6200410	ITX 19 B T40	M 7 - M 8	6,65	55	17	2,92 x 3,28	65
6200840	ITX 19 B T45	M 8 - M 10	7,82	55	17	3,45 x 3,68	70
6201300	ITX 19 B T50	M 10	8,83	55	17	3,83 x 3,78	90
6202700	ITX 19 B T55	M 12	11,22	55	15	4,85 x 4,79	110
6203270	ITX 19 B T60	M 14	13,25	55	15	5,63 x 7,87	110

