





P+L Systems™

EYOCUTOR



Market leading high quality flykiller...



P+L Systems™



Market leading high quality flykiller

As the biggest selling range of quality electronic flykillers in Europe, **Exocutor™** is ideal for any application where a high quality electronic flykiller is required at a competitive price. Incorporating high specification components and build quality, **Exocutor™** is available as a 6, 16, 30 or 40W unit in either white or stainless steel construction.

Features

Market leading design

Contemporary British design

High quality components

Reliable high specification 3750V transformer

High efficacy UV tubes

Proven to be more effective and longer lasting than standard UV tubes

Robust construction

Strong UV stable polycarbonate and coated mild steel / stainless steel construction

Flexible and easy installation

Wall, ceiling or desk mounting

Innovative killing grid

Unique triangular killing grid for a larger effective catch area

Easy cleaning and service

Deep mains interlocked removable catch tray with anti-crawl out edges

Independent certification

Independently tested and certified to RoHS and relevant European standards

Complete peace of mind

Two year guarantee (excluding tubes)



EX 6



EX 16



EX 30




EX 40

Specification:

Part No.	Model	Dimensions(mm)	Coverage	Tubes	Weight	Colour
Z050	EX6	270x140x260	20m ²	1x6W	3.5 kg	White
Z060/63	EX 16	360x140x260	40m ²	2x8W	4 Kg	White or Stainless
Z061/64	EX30	510x140x260	80m ²	2x15W	6.5 Kg	White or Stainless
Z062/65	EX40	660x140x260	120m ²	2x20W	8.5 Kg	White or Stainless

Traditional killing grid cross section



Triangular killing grid cross section

