

	CONTACT TOP 78mm 25.5mm 14.5mm 6mm Ø 2mm 6.5mm BOTTOM 50mm 3mm Ø LATERAL 27mm LATERAL 24mm 3mm ENDS 14.5mm 11mm 9.5mm Ø 6mm Ø PHOTO	MAGNET 78mm 25.5mm 14.5mm 6mm Ø 2mm 50mm 3mm Ø 27mm 24mm 3mm 14.5mm 11mm 14.5mm 11mm	DESCRIPTION Grade 2, Class III angle contact 4 core cable prefitted. 1m length. Single reed, normally closed. (Complete circuit when magnet present). VARIANTS None. ACTIVATION Reed switch, ~50mm operating gap. WIRING Yellow/Red REED Black/Blue TAMPER LOOP MATERIALS Anodised AA15 aluminium casting. Ferrite/Alnico V magnet. Rhodium reed. TEMPERATURE RANGE -40 to +50 degrees Celsius. ELECTRICALLY RATED AS FOLLOWS 500mA Max DC. 500mA Max AC. 1 – 100v DC. 125v AC Max.
--	---	--	---



KNIGHT
FIRE & SECURITY

Unit 84 Seawall Road Ind. Estate
Cardiff UK CF24 5TH
Tel: +44 (0) 2920 488 129
Fax: +44(0) 2920 489 132

Drawing #: H10C
Drawn: Gareth Carpenter
Date: 01/07/2017
Revision: 1

All dimensions in mm
Do not scale



© Knight Fire & Security Products Ltd
All cases of infringement will be pursued.