



PRODUCT SPEC SHEET

SKU 812-27

Model:VT-8633

EAN:3800170254879

VT-8633 8W/16W/20W LED DOME LIGHT (EMERGENCY/SENSOR) 3IN1 RD IP54



IP54
STANDARD

03 YEAR
WARRANTY

Super Bright
120
LUMENS/W

- Uses High Quality Power Driver and LED Chip
- Built-in switch for CCT and Wattage changing
- Powerful LED light source with lumen efficiency of 120 LM/W
- Hinged LED gear tray for easy installation
- Emergency backup for more than 3 Hours
- High frequency microwave sensor for efficient detection over barriers
- IP54 Ingress protection
- IK protection IK08
- Withstands weather, dust and vandalism
- Applications - Passage, Exterior walls, Airport, Malls, Security Lighting etc
- Maintained operation

TECHNICAL INFORMATION

Color Temperature:	3IN1
Model:	VT-8633
Detection Range:	Max D:6mx3m
Battery Charging Current:	250mA
Battery Discharge Current:	410mA
Detection Motion Speed:	0.5-3m/s
Ambient Light:	Day,2lux,10lux,25lux,50lux optional
Emergency Standby Watts:	1.2

LISTING DETAILS

SKU:	812-27
Model:	VT-8633
EAN:	3800170254879
Commodity Code:	94051140

PACKAGING

Gross Weight (Kgs):	1.36
Unit CBM:	0.013565
Dimension:	320x100mm

MASTER BOX PACKAGING

Hold Time:	5s, 30s, 90s, 3min, 20min, 30min
Dimmable:	No
Emergency Operation Time:	>3 Hours
Detection Angle:	360°Ceiling/120°Wall Mounted
Detection Distance:	3-6m
Battery Type:	LiFePO4, 3.2V 2Ah Battery
CRI:	>80
Watts:	20
Lumens:	2600
Input Power:	AC:200-240V, 50Hz
Unit Color:	White
Color for Web:	3IN1
Body Type:	PC
Dimension:	320x100mm
Shape:	Round
PF:	>0.9
LED Chip Type:	SMD
Beam Angle:	110°
Energy Rating Label:	E (2021)
Sensor Type:	Microwave Sensor
IP Rating:	IP54
IK Rating:	IK08
Long Life:	30,000 Hours
lumens per watt:	120

Box Qty:	10
Qty Per Pallet:	
Length (Box) mm:	330
Width (Box) mm:	110
Height (Box) mm:	330