



PRODUCT SPEC SHEET

SKU 104806

Model:VT-61006CCT

EAN:3800170256811

VT-61006CCT 6W BACKLIT RECESSED PANEL CREE CHIP 3IN1 SQ 6YRS WTY



IP20
STANDARD



- Strong and sturdy Plastic body Backlit Mini Panels
- High quality power driver ensures reliable lifetime
- Choose and switch to your preferred color temperature at any time using the CCT switch
- Designed with high efficiency LED SMD-CREE Chip chips.
- No Lead or Mercury content hence Environment friendly
- Suitable for offices, conference rooms, showrooms, lobbies, cabins, kitchens etc.

TECHNICAL INFORMATION

Color Temperature:	3IN1
Model:	VT-61006CCT
On/Off Cycles:	>15000
Dimmable:	No
Installation Type:	Recessed
CRI:	>80
Watts:	6
Lumens:	630
Input Power:	AC:220-240V, 50/60Hz
Unit Color:	White
Color for Web:	3IN1
Body Type:	Plastic
Dimension:	120.5x120.5x28.4mm
Operation Temperature:	-20°C to +45°C

LISTING DETAILS

SKU:	104806
Model:	VT-61006CCT
EAN:	3800170256811
Commodity Code:	94051140

PACKAGING

Gross Weight (Kgs):	0.12
Unit CBM:	0.000851
Dimension:	120.5x120.5x28.4mm

MASTER BOX PACKAGING

Box Qty:	80
Qty Per Pallet:	1920
Length (Box) mm:	136

Shape:	Square
LED Chip Type:	SMD-CREE Chip
Beam Angle:	120°
Energy Rating Label:	F (2021)
IP Rating:	IP20
Energy Saving:	85 Energy
Long Life:	30,000 Hours
lumens per watt:	105

Width (Box) mm:	38
Height (Box) mm:	136