



PRODUCT SPEC SHEET

SKU 24153

Model:VT-11148CCT

EAN:3800170254343

VT-11148CCT 0.9W LED SOLAR WALL LIGHT 3IN1 BLACK BODY IP54 WITH REMOTE CONTROL



IP54
STANDARD

03
YEAR
WARRANTY

- Zero electricity cost - Solar Powered
- DC 5V 2.3W Monocrystal Solar Panel
- Charging 6-8 Hours, Working 10-12 Hours
- IP54 protection safe for outdoor use
- Easy installation, Cordless to install
- Suitable for gate, garden, balcony, pavilions, stairs, roof, fence, courtyard etc

TECHNICAL INFORMATION

Color Temperature:	3IN1
Model:	VT-11148CCT
Working Time:	10-12 Hours
Battery Type:	DC:3.7V Li-ion 1800mAh Battery
Lumens:	120
Unit Color:	Black
Color for Web:	3IN1
Dimension:	190x100x220mm
LED Chip Type:	SMD
Beam Angle:	84°
Solar Panel:	DC 5V 2.3W Monocrystal
Charging Time:	6-8 Hours
IP Rating:	IP54

LISTING DETAILS

SKU:	24153
Model:	VT-11148CCT
EAN:	3800170254343
Commodity Code:	94054131

PACKAGING

Gross Weight (Kgs):	0.66
Unit CBM:	0.00508
Dimension:	190x100x220mm

MASTER BOX PACKAGING

Box Qty:	20
Qty Per Pallet:	200

IK Rating:	IK02	Length (Box) mm:	215
		Width (Box) mm:	105
		Height (Box) mm:	200