



PRODUCT SPEC SHEET

SKU 232026

Model:VT-44153

EAN:3800170254930

VT-44153 150W FLOODLIGHT CREE CHIP 6500K BLACK BODY GREY GLASS 135LM/W 6YRS WARRANTY



IP65
STANDARD



- New Range of LED Floodlights powered with high quality SMD-CREE Chip
- Product designed with high lumen efficiency of 135 LM/W
- Built Strong and durable with Aluminium - Corrosion resistant design
- IP65 rated outdoor protection with a warranty period of 6 Years
- Suitable for building facades, sports facilities, industrial, commercial billboards, hoardings, parking lots etc.

TECHNICAL INFORMATION

Color Temperature:	6500K
Model:	VT-44153
Instant Start:	0-100% in <1s
Dimmable:	No
CRI:	>70
Watts:	150
Lumens:	20250
Useful Lumens:	17220
Input Power:	AC:220-240V, 50Hz
Unit Color:	Black
Color for Web:	White
Body Type:	Aluminium
Dimension:	331x47x278mm
Operation Temperature:	-20°C to +45°C

LISTING DETAILS

SKU:	232026
Model:	VT-44153
EAN:	3800170254930
Commodity Code:	94054210

PACKAGING

Gross Weight (Kgs):	1.98
Unit CBM:	0.006328
Dimension:	331x47x278mm

MASTER BOX PACKAGING

Box Qty:	4
Qty Per Pallet:	200
Length (Box) mm:	336

LED Chip Type:	SMD-CREE Chip
Beam Angle:	115°
Energy Rating Label:	D (2021)
Wire Length:	1m
IP Rating:	IP65
Energy Saving:	85 Energy
Long Life:	30,000 Hours
lumens per watt:	135

Width (Box) mm:	52
Height (Box) mm:	293