



PRODUCT SPEC SHEET

SKU 23089

Model:VT-48500

EAN:3800170210462

VT-48500 500W SUPER HIGH POWER LED FLOODLIGHT 1M CABLE 4000K BLACK BODY IP65 135LM/W



IP65
STANDARD

02
YEAR
WARRANTY

- High performance light for outdoor applications
- Fitted with high efficiency SMD LED Chips that offer up to 85% in energy savings
- IP65 rated solid ingress protection
- Experience hassle-free setup with the provided 1-meter cable
- Excellent Heat dissipation
- Suitable for lobby, garage, passage, parking lot and outdoor areas

TECHNICAL INFORMATION

Color Temperature:	4000K
Model:	VT-48500
Instant Start:	0-100% in < 1s
On/Off Cycles:	>15000
Dimmable:	No
CRI:	>70
Watts:	500
Lumens:	67500
Input Power:	AC:220-240V, 50Hz
Unit Color:	Black
Color for Web:	Day White
Body Type:	Diecast Aluminium
Dimension:	530x65x523mm

LISTING DETAILS

SKU:	23089
Model:	VT-48500
EAN:	3800170210462
Commodity Code:	94054210

PACKAGING

Gross Weight (Kgs):	8.52
Unit CBM:	0.046405
Dimension:	530x65x523mm

MASTER BOX PACKAGING

Box Qty:	1
Qty Per Pallet:	30

Operation Temperature:	-20°C to +45°C
PF:	>0.9
LED Chip Type:	SMD
Downward LOR (%):	99.6
ULR (%):	0.0
Energy Rating Label:	D (2021)
IP Rating:	IP65
IK Rating:	IK05
Energy Saving:	85 Energy
Long Life:	25,000 Hours
lumens per watt:	135
EMC Certificate:	Check the certificate
LVD Certificate:	Check the certificate
ROHS Certificate:	Check the certificate

Length (Box) mm:	600
Width (Box) mm:	135
Height (Box) mm:	600