

Pos	pcs.	TG part number	description	remarks
1	1	J01020A0110	N Straight Plug Crimp	crimp/crimp
2	1	J01020A0110	N Straight Plug Crimp	crimp/crimp
3	3000 mm	L01002A0000	RG-214	50 Ohm
4	1	B00101B0003	shrink sleeve	30 mm
5	1	B00101B0003	shrink sleeve	30 mm
6	0		labeling left	
7	0		labeling middle	
8	0		labeling right	

Technical Data:

cable:

cable name: RG-214
 impedance: 50 Ohm
 total length: 3000 mm
 cable tolerance according to DIN 47101: 2964 mm $\pm$ 40 mm
 cable cut length: 3004 mm -80 mm

connector left:


connector name: N Straight Plug Crimp
connector design: straight
protection: shrink sleeve
assembly construction code: B3412

connector right:

connector name: N Straight Plug Crimp
connector design: straight
protection: shrink sleeve
assembly construction code: B3412

quality check program number: L03200A0001

For your information only! Coax Configurator is subject to technical verification!

2015	date	name			prod.order.no.
	11.06.2015	autom.			
scale	title				 Telegärtner
	RF – cable assembly				
dim. without tolerances according to	doc.type	ref.no.			 dimensions: mm
		L09999B3618			
	RoHS compliant				Original: DIN A4