

142-1701-831

Transceivers

SMA Jack | High Frequency Self Fixture End Launch | .015 Contact

Specification

PN	142-1701-831
Category Name	RF & Microwave Connectors
Description	SMA Jack High Frequency Self Fixture End Launch .015 Contact
Series	SMA
Type	High Frequency
Termination Type	Solder
Termination Style	Receptacle
Gender	Jack
Max Frequency [GHz]	26.5
Mounting Style	End Launch
Body Style	Straight
Body Material	Brass
Body Finish	Gold
Contact Material	Beryllium Copper
Contact Plating	Gold
Insulator	PTFE
Max Frequency (GHz)	26.5
Durability (Cycles Min)	500
Operating Temperature Range (°C)	-65 to +165
Impedance (Ohms)	50
Working Voltage (Vrms)	170
Insulation Resistance (mOhms Min)	1000
Number of Ports	1
Brand	Johnson

