




XH CONNECTOR



2.5mm Pitch/Wire-to-Board Connectors/Crimp Style and Mating Style



Part Number:

- ASXHSXH22B254

Description:

- JST Series – [XH Series](#)
- Pitch – 2.5mm
- Cable length (inside dimension) – 254mm

Material Specification:

- (1) Terminal: SXH-001T-P0.6
- (2) Cable Type: UL1007
- (2) Cable Size: 22AWG
- (2) Cable Colour: Blue

Accessories:

- Extraction Tool: XJ-06

Quality

- We trust and believe in our product. Each step of our development and manufacturing process is focused on delivering a fault-free product. JST does not compromise on quality.

Applicable Housings:

No. of Circuits	Part Number
1	XHP-1
2	XHP-2
3	XHP-3
4	XHP-4
5	XHP-5
6	XHP-6
7	XHP-7
8	XHP-8
9	XHP-9
10	XHP-10
11	XHP-11
12	XHP-12
13	XHP-13
14	XHP-14
15	XHP-15
16	XHP-16
20	XHP-20

Additional Information:


Alternative Colours and length cables are available upon request, please contact JST for further details by e-mailing jukma@jst.co.uk



XH CONNECTOR



2.5mm Pitch/Wire-to-Board Connectors/Crimp Style and Mating Style



A SXH SXH 22 B 254

Supply Form: Assembled Wire

Terminal Part Number end A: SXH-001T-P0.6

Terminal Part Number end B: SXH-001T-P0.6

Cable Size: 22awg (??AWG)

Cable Colour: B (Blue), K (Black), R (Red), N (Brown), H (Grey)
O (Orange), Y (Yellow), W (White), M (Green), P (Purple), PK (Pink)

Cable Length: 254mm (????mm)

Additional Information:

Alternative Colours and length cables are available upon request, please contact JST for further details by e-mailing jukma@jst.co.uk